

Electronic depth callipers

IP40

ORION[®]

Application:

For measuring, e. g. bore depths, shoulders on workpieces etc.

Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- ABS function

Delivery:

in a plastic case, with battery (1 x type SR44)



Art. no.	31295 115
Brand	ORION
Manufacturer Part Number	31295115
Min./max. length measuring range	0-150 mm
Digit increment	0.01 mm
IP protection class	IP 40
Bridge length x bridge width	80 x 7 mm
Type of locating	With locking screw
Calibration Group	B
With automatic shut off	Yes
Number of rechargeable batteries/batteries	1 PCS
Display	Digital
Battery designation	1,5 V SR44
ISO	13385-2
Bridge length	80 mm
Gross Weight	0.397 kg
Product Group	3BI

EAN

4053625306442