

Ring bolt

Screwable sling point, 360° rotation

CARTEC

Application:

For the safe attachment of loads.

Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing



Art. no.	77232 136
Brand	CARTEC
Manufacturer Part Number	C807XHT36
Design	Without key
Thread dimension	M36
Load-carrying capacity	7 t
Distance between lower edge of retainer holder and retainer	105 mm
Bracket width	30 mm
Bracket height	32 mm
Outer diameter	135 mm
Diameter 2	96.5 mm
Internal width	74 mm
Width of support plate	77 mm
Usable thread length	55 mm
Width across flats	22 mm
Weight	3.4 kg
Gross Weight	3.346 kg
Product Group	775

EAN

8013429916182