





## Other Special Lamps

|   |  |
|---|--|
|  | <b>Type SI2322</b><br><b>110V 100W E27</b>     |
|   | <b>Ordering - No.</b><br><b>62322</b>          |
| <b>Product Description</b>  | Special Incandescent Lamp                      |
| <b>Features</b>   | Softglass Bulb,<br>Exactly positioned Filament |
| <b>Applications</b>   | Locomotive Headlight                           |

## Technical Details

|                          |   |
|--------------------------|---|
| Type                     | SI2322  |
| Rated Voltage (V)        | 110   |
| Wattage (W)              | max. 110  |
| Luminous Flux (lm)       | 1200 -12%   |
| Average Lifetime (h)     | 500   |
| Base                     | E27   |
| Bulb Diameter (mm)       | max. 61,0   |
| Light Center Length (mm) | 76,0 ± 3,0  |
| Operating Position       | vertical, Base down<br>(± 45°)  |
| Packaging Configuration  | 100 pcs.  |
| Environmental Remark     | Product don't contain lead or mercury and is conform with Directive 2002/95/EC "Restriction of the use of certain hazardous substances in electrical and electronic equipment". |

## Drawing (in mm)



|             |                         |
|-------------|-------------------------|
| valid from  | 05.03.2014—V2—PN14/0072 |
| replace for | 31.01.2013—V1           |
| file        | 62322.100.pdf           |