

PRODUCT SPECIFICATION

Brand	KASP
Product Range	Steel padlocks
Catalogue number	180
Date	18/01/2008

<p>Range Description Open and Close shackle steel padlocks</p>				
<p>Features</p> <ul style="list-style-type: none"> • Hardened steel shackle – extra protection from hacksaw and cropping attacks • Double ball bearing locking mechanism – extra strength to resist torsion and pull attacks • Chrome plated steel body – extra strength & resistance to corrosion • 5 Pin cylinder featuring paracentric keyway and anti pick mushroom pins for extra protection against picking • The close shackle version offers additional shackle protection to resist shackle attack • Weather rating: 2 <p>Both padlocks are supplied display packed, in sealed blister packs.</p> <p>2 Keys are supplied with each padlock</p>				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
K18060D	Steel Padlock 60mm – display packed	5013969901139	83011000	3
K18060XD	Steel Padlock 60mm Close Shackle – display packed	5013969901146	83011000	3

K18060KB	Key Blank for 180 Series	5013969902075	83017000	100
K18060	Steel Padlock 60mm – boxed	5013969902990	83017000	3
K18060X	Steel Padlock 60mm Close Shackle – boxed	5013969903010	83017000	3
K18060KA	Steel Padlock 60mm Keyed alike – boxed	5013969903003	83017000	1
K18060XKA	Steel Padlock 60mm Close Shackle Keyed alike – boxed	5013969903027	83017000	1
K16080MK	Steel Padlock 60mm Master keyed – boxed	5013969903041	83017000	1
K16080XMK	Steel Padlock 60mm Close Shackle Master keyed – boxed	5013969903058	83017000	1

<p>Technical product information</p>	<p>Body - Steel, Chrome plated</p> <p>Shackle- Hardened steel, Chrome plated</p> <p>Locking mechanism- Pin tumbler cylinder type, 5 pin cylinder, Brass pins – Driver pin 5 is plain, driver pins 1 to 4 are mushroom type.</p> <p>Key differs- 1988</p> <p>Re-keyable – Yes</p> <p>Security rating:</p> <table border="1" data-bbox="490 949 878 1087"> <thead> <tr> <th>Type</th> <th>Security rating</th> </tr> </thead> <tbody> <tr> <td>K18060</td> <td>11</td> </tr> <tr> <td>K18060X</td> <td>13</td> </tr> </tbody> </table> <p>Shackle Dimensions:</p> <table border="1" data-bbox="490 1199 1216 1386"> <thead> <tr> <th rowspan="2">Dimensions mm</th> <th colspan="3">Shackle</th> <th>Body</th> </tr> <tr> <th>Dia</th> <th>Internal width</th> <th>Internal height</th> <th>Width</th> </tr> </thead> <tbody> <tr> <td>K18060</td> <td>12</td> <td>34</td> <td>28</td> <td>60</td> </tr> <tr> <td>K18060X</td> <td>12</td> <td>35</td> <td>27</td> <td>60</td> </tr> </tbody> </table> <p>Use environment- Normal outdoor use</p> <p>Recommended applications- Garages, Shutters, Vehicles and Site gates</p>	Type	Security rating	K18060	11	K18060X	13	Dimensions mm	Shackle			Body	Dia	Internal width	Internal height	Width	K18060	12	34	28	60	K18060X	12	35	27	60
Type	Security rating																									
K18060	11																									
K18060X	13																									
Dimensions mm	Shackle			Body																						
	Dia	Internal width	Internal height	Width																						
K18060	12	34	28	60																						
K18060X	12	35	27	60																						
Standards compliance	None applicable																									
User health and safety information	None applicable																									
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations																									
Material safety data	None applicable																									
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not																									

	covered
Country of origin	China

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K18060D	60	27	98	628	150	35	190	696
K18060XD	60	27	98	726	150	35	190	797
K18060KB	23	3	54	10	-	-	-	-
K18060	60	27	98	628	70	115	40	680
K18060X	60	27	98	726	70	115	40	770
K18060KA	60	27	98	628	70	115	40	680
K18060XKA	60	27	98	726	70	115	40	770
K16080MK	60	27	98	628	70	115	40	680
K16080XMK	60	27	98	726	70	115	40	770

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K18060D	160	270	70	2177		
K18060XD	160	270	70	2480		
K18060KB	120	120	40	1061		
K18060	120	125	85	2102		
K18060X	120	125	85	2372		
K18060KA	-	-	-	-		
K18060XKA	-	-	-	-		
K16080MK	-	-	-	-		
K16080XMK	-	-	-	-		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K18060D	37	Blister	8	Backing card			89	Box
K18060XD	37	Blister	8	Backing card			89	Box
K18060KB					8	Bag		
K18060			30	Box			62	Box
K18060X			30	Box			62	Box
K18060KA			30	Box				
K18060XKA			30	Box				
K16080MK			30	Box				
K16080XMK			30	Box				