


★★★★★
BLUE-LINE® External Micrometer
 DIN 863


- for standard expectations
- drum and sleeve matt chrome finish
- frame hammer blow grey lacquered, with insulation plates
- carbide surfaces, lapped, spindle hardened and ground
- locking lever for quick and precise fixing
- with ratchet for constant measuring pressure
- with adjustment key, from up 25 mm with setting gauge



ART No	mm	mm	ø mm	mm	A mm	B mm	D mm	L mm	max. mm	KG	ART No CC
231351	0 - 25	0.01	18	0.5	6	24	3.0	32	0.004	0.170	2394000
231352	25 - 50	0.01	18	0.5	8	32	3.0	57	0.004	0.270	2394001
231353	50 - 75	0.01	18	0.5	8	45	3.0	82	0.005	0.340	2394001
231354	75 - 100	0.01	18	0.5	8	57	3.0	107	0.005	0.440	2394001
231355	100 - 125	0.01	18	0.5	8	70	3.0	133	0.006	0.640	2394002
231356	125 - 150	0.01	18	0.5	8	82	3.0	158	0.006	0.890	2394002
231357	150 - 175	0.01	18	0.5	8	95	5.5	183	0.007	1.100	2394002
231358	175 - 200	0.01	18	0.5	8	107	5.5	209	0.007	1.230	2394002

★★★★★
BLUE-LINE® External Micrometer
 DIN 863

- with inch graduation
- for standard expectations
- drum and sleeve chrome finish
- frame hammer blow grey lacquered, with insulation plates
- carbide surfaces, lapped, spindle hardened and ground
- locking lever for quick and precise fixing
- with ratchet for constant measuring pressure
- with adjustment key, from up 1 inch with setting gauge



ART No	inch	inch	ø mm	mm	A mm	B mm	D mm	L mm	max. mm	KG	ART No CC
231371	0 - 1	0.0001	18	0.5	6	24	3.0	32	0.004	0.170	2394000
231372	1 - 2	0.0001	18	0.5	8	32	3.0	57	0.004	0.270	2394001
231373	2 - 3	0.0001	18	0.5	8	25	3.0	82	0.005	0.340	2394001
231374	3 - 4	0.0001	18	0.5	8	57	3.0	107	0.005	0.440	2394001