


# VOLTAGE TESTER

## TP3000LED



Residential



Industry



- 2-pole voltage tester with LED indicator scale
- ac/dc voltage indication range from 12 to 750 V
- Phase detection test
- Phase sequence
- Continuity and diode test
- White light LED torch
- Tip adapters for selection of 2 or 4 mm diameter probe tips
- IP65 for outdoor use
- CATIV 600V safety category
- In compliance with IEC/EN 61243-3:2014

# TP3000LED

## VOLTAGE TESTER

General	
Vac/dc LED Indicators scale	✓
IP	IP65
Auto power off	✓
Batteries	AAA x2(R03, LR03, 24D, 24A)
Dimensions	239mm x 68mm x 29mm
Weight	230 g
Standards in compliance	IEC/EN 61243-3:2014
Safety category	CAT IV 600V, CAT III 1000V

Specs	
AC/DC Voltage	12-750V
AC Frequency	45-65Hz
Single phase test	100V-750V
Phase rotation test	100V-750V
Continuity Buzzer	✓

Product Code Information	
SKU	KPSTP3000LEDCBINT
EAN Code	8435394786261
UPC Code	810053676868
Pcs/export carton	20