

CAB PCQ 604027 T

FIBOX
Enclosing innovations



Sample image

Order symbol: CAB PCQ 604027 T

EAN: 6418074011138

Product nbr: 8113178


El. number:

Description: Enclosure. PC

- Finland: 3421932
- Denmark:
- Sweden: 2540111

Remarks: Smoked transparent cover

Including: Base with screws for mounting plate/DIN-rail. internal corner plugs. cover with PUR gasket and CS 12137 cover screws.



Dimensions:	Height	Width	Depth
mm:	600	400	270
inch:	23.62	15.75	10.63

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	Clear transparent
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120
Temperature °C (continuous):	-40 ... 80
Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175

Accessories:

EKIV 64H	Back Panel, for enclosures: (570 x 370 x 1)
PAT 12040	Hinge kit
MB 12225 AL	Swing door kit
EKIV 37	DIN-35 Mounting rail, for enclosures: (366 x 35 x 1)
DRF 63/64	DIN rail frame kit, for enclosures:
FP A 64	Swing-out door/Front panel (aluminum), for enclosures: (568 x 368 x 1)

Rating:

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK08;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5*
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	

Certificates:

Certificate FI 4084B