

Within Series Adaptor 34_SMA-50-0-51/199_N

Description

Bulkhead adaptor jack/jack
SMA jack (female) / SMA jack (female)



Interface standard
Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz
VSWR DC - 18 GHz
≤ 1.05 + 0.005 f (GHz)

Mechanical Data

Number of matings 500
Weight 0.0038 kg

Environmental Data

Operating temperature -65 °C to 125 °C
2011/65/EU (RoHS) compliant

Material Data

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DCA-00013642
Mounting hole DOU-00008731

Ordering Information

Single package 34_SMA-50-0-51/199_NE