

## Han D F Crimp Contact CuNi



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 6261
Specification	Han D F Crimp Contact CuNi
HARTING eCatalogue	<a href="https://b2b.harting.com/09150006261">https://b2b.harting.com/09150006261</a>

### Identification

Category	Contacts
Series	Han D <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Rated current	≤10 A
Contact resistance	≤1 mΩ
Stripping length	8 mm

### Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Yes
--------------------------------------	-----

California Proposition 65 substances	Nickel
--------------------------------------	--------

## Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

## Commercial data

Packaging size	25
----------------	----

Net weight	0.2 g
------------	-------

Country of origin	Germany
-------------------	---------

European customs tariff number	85366990
--------------------------------	----------

GTIN	5713140022201
------	---------------

ETIM	EC000796
------	----------

eCl@ss	27440204 Contact for industrial connectors
--------	--