

# NADB15FF-B

15 pole D-SUB feedthrough, female to female, black D-shape housing

## Features & Benefits

---

- Ideal for audio networking and integration of equipment into video systems
- Universally accepted standard D-shape housing



## Technical Information

---

### Product

|        |                 |
|--------|-----------------|
| Title  | NADB15FF-B      |
| Gender | female - female |

### Electrical

|                               |            |
|-------------------------------|------------|
| Contact resistance            | 30 mΩ      |
| Insulation resistance         | > 5 GΩ     |
| Number of electrical contacts | 15         |
| Rated current per contact     | 3 A        |
| Rated voltage                 | 50 V ac    |
| Dielectric strength           | > 0.5 kVac |

### Mechanical

|                    |                |
|--------------------|----------------|
| Panel thickness    | 4 mm           |
| Wiring             | Feedthrough    |
| Mounting direction | Front mounting |
| Chassis shape      | D              |

## Material

|                 |                         |
|-----------------|-------------------------|
| Contact plating | Au                      |
| Contacts        | Brass (CuZn39Pb3)       |
| Insert          | Steel , tin plated, PBT |
| Shell           | Zinc diecast (ZnAl4Cu1) |
| Shell plating   | Black chromium          |

## Environmental

|                   |                  |
|-------------------|------------------|
| Flammability      | UL 94 V-0        |
| Temperature range | -25 °C to +85 °C |

## Accessories

### SCCD-W



### SCDX



### SCDP-\*



### NZP1RU-12



### NZP1RU-8

