

## Angular milling cutter 90° with shank

For indexable milling inserts APKT..1003..

**ORION**<sup>®</sup>

### Execution:

- Bronzed, with robust support design
- Soft cutting by positive installation position of the reversible tip
- For groove milling, circumferential milling and heel milling
- Smooth milling behaviour of the tools

### Advantage:

- Axial run-out max. 0.03 mm
- Concentricity max. 0.03 mm
- precise 90° angular milling

### Delivery:

1 pc. Carrier incl. reversible tip screws, without tips



<b>Art. no.</b>	<b>16017 037</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	16017037
<b>Cutting edge diameter</b>	25 mm
<b>Clearance length</b>	49 mm
<b>Length</b>	105 mm
<b>Shank diameter</b>	25 mm
<b>max. ap</b>	8 mm
<b>Number of cutting edges</b>	4 PCS
<b>Number of cutting inserts</b>	4
<b>Gross Weight</b>	0.350 kg
<b>Product Group</b>	148

### EAN

4053625270897