

Electronic micrometer MICROMASTER IP54



Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

Execution:

- Carbide measuring faces
- Advanced friction coupling for consistent, repeatable measuring force
- Zero setting at any position
- mm/inch switch-over
- Auto off
- Preset function
- ABS function
- Display blocking function

Delivery:

In a case, with battery (1 x 3 V lithium, type CR 2032)



Art. no.	31408 025
Brand	TESA
Manufacturer Part Number	06030021
Display	Digital
Min./max. length measuring range	25-50 mm
Digit increment	0.001 mm
Measuring surface diameter	6.5 mm
IP protection class	IP 54
Spindle clamping	Yes
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
DIN	863
Measuring spindle increments	0.5 mm
Gross Weight	0.780 kg
Product Group	362

EAN

7630041116304