

Pneumatic blow-out gun

Multi-duct nozzle

Application:

For targeted and precise blowing out of workpieces and injection moulded parts.

Execution:

- Compressed air flow regulated via counter screw
- Nozzle made from steel, therefore no breakage of nozzle tip
- Noise level at 6 bar = 79 dB(A)

Delivery:

In cardboard box



Art. no.	75179 200
Connection thread	G 1/4 inch
Max. operating pressure	10 bar
Inner hose diameter	6 mm
Nozzle size	65 mm
Material	Steel
Sound-pressure level	79 dB
Gross Weight	0.227 kg
Product Group	753