



SIL SOCKETS „THROUGH HOLE”
ID: 008 MS-ULP ultra low profile

Series 103



TECHNICAL DATA

Pitch	2,54 mm
Insulating Material	high temp. thermoplast UL94V-0
Contact Material	Brass/BeCu
Rated Current	1 Amp.
Rated Voltage	100 V _{RMS} /150 V _{DC}
Breakdown Voltage	min. 1000 V _{RMS}
Operating Temperature	-55°C bis +125°C
Maximum Soldering Temperature	260°C for 10 seconds



All dimensions in mm.
 Other dimensions upon request.

MS-ULP XX SXX U

Poles: 1 - 64 poles possible

XX: TG = sleeve: Sn/clip: Au
 TG 8 = sleeve: Sn/clip: 0,75µm Au

U: RoHS-compliant with high temp. plastic