


VIEWING DIRECTION  
6:00

1	REV.	MODIFY CONTENT	DATE
	DWN	Bauing	
	CKD	SCALE	MODEL
	APPD	DATE	MODEL
			M201202/C(6.35)8R1G
			JAN-31-05



	COM		COM
1	COM	21	1A
2	≡	22	1F
3	K	23	1G
4	.	24	2B
5	.	25	2A
6	.	26	2F
7	.	27	2G
8	4DP	28	L
9	3E	29	3B
10	3D	30	3A
11	3C	31	3F
12	3DP	32	3G
13	2E	33	.
14	2D	34	.
15	2C	35	.
16	2DP	36	.
17	1E	37	.
18	1D	38	LO BAT
19	1C	39	1B
20	1B	40	COM

NOTE:

1. TN TYPE
2. DRIVING METHOD: STATIC
3. OPERATING VOLTAGE: 3.0 V
4. OPERATING TEMP: -0 ~ 50°C
5. STORAGE TEMP: -10 ~ 60°C
6. VIEWING DIRECTION: 6:00
7. POLARIZER MODE: REFLECTIVE POSITIVE
8. CONNECTION: PIN TYPE
9. DIMENSIONS ARE IN MILLIMETERS AND UNLESS OTHERWISE NOTED ARE ±0.20MM

1					
REV.	MODIFY CONTENT				DATE
DWN	Bowing	UNIT	mm	CUST. MODEL	
CKD		SCALE		MODEL	M201202/C(6.35)8R1G
APPD		DATE			JAN-31-05



**MESOSTATE LCD INDUSTRIES CO., LTD**