



**FEATURES**

Double tuning fork type contact guarantees high reliability.  
 1.27MM pitch Low-Profile mini type Match to 0.4mm sq. posts.

**MATERIAL**

- Insulator . . . . . NY-66
- Contact . . . . . Gold Plated
- Terminal . . . . . 5191 Phosphor Bronze

**SPECIFICATIONS**

- Current Rating: 1 amperes MAX
- Contact Resistance: 30m MAXΩ
- Insulation Resistance: 1000 megohms MAX
- Dielectric Withstanding Voltage: AC 650 volts RMS at sea level

\* 以下圖示塑膠公差皆為±0.20  
 金屬件公差為±0.05

RoHS Compliant		<b>HSM</b> 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准 Ivy	 TOLERANCE 容許公差 0 ± .00 ± ANG. ±	PART NAME 品名 1.27mm MINI JUMPER 2P H:3.0mm CLOSE COVER GOLD PLATING BLACK COLOR ROHS LOW-LEAD	
DWG. 製圖 Yumi			
DATE 制表日 2010/04/15	UNIT 單位 MM	SIZE. 紙張尺寸 A4	PART NO. 料號 C2740-02GBGB00R
PAGE 張數 1 OF 1	REV. 版次 A		