# **Product leaflet**

**Product** Model No. Ordering No. Gas filter ABEK1 SR 297 H02-5312

### **Product Description**

Gas filter SR 297, Class 1, is designed for use together with Sundström half masks and full face masks. The filter is of type ABEK and provides protection against the following types of gases and vapours:

Type A protects against organic gases and vapours, such as solvents, with boiling points > +65 °C.

Type B protects against inorganic gases and vapours, such as chlorine, hydrogen sulphide and hydrogen

Type E protects against acidic gases and vapours, such as sulphur dioxide and hydrogen fluoride.

Type K protects against ammonia and certain amines, such as ethylene diamine.

The gas filter can easily be combined with particle filter SR 510 P3 in order to obtain protection also against aerosols (particles), e.g. during spray painting.

## **Technical specification**

	SR 297 ABEK1	EN 14387:2004
Pressure drop at 30 l/min	≈ 85 Pa	≤ 100 Pa
Diameter/height	106/36 mm	-
Weight	≈ 160 g	≤ 300 g
Service temperature	-10 – +55 °C, < 90 % RH	
Storage temperature	-20 – +40 °C, < 90 % RH	
Resistance time		
A1, Cyclohexane C <sub>6</sub> H <sub>12</sub> , 1,000 ppm	> 110 min	≥ 70 min
B1, Chlorine Cl <sub>2</sub> , 1,000 ppm	> 30 min	≥ 20 min
B1, Hydrogen Sulphide H <sub>2</sub> S, 1,000 ppm	> 60 min	≥ 40 min
B1, Hydrogen Cyanide HCN, 1,000 ppm	> 40 min	≥ 25 min
E1, Sulphur Dioxide SO <sub>2</sub> , 1,000 ppm	> 25 min	≥ 20 min
K1, Ammonia NH₃, 1,000 ppm	> 65 min	≥ 50 min
Approval	EN 14387:2004	

- A. Activated carbon
- B. Filter disc
- C. Marking label
- D. Filter case



#### **Head Office**

Vasavägen 84

SE-181 10 Lidingö

Tel: +46-(0)8-562 370 00 Fax: +46-(0)8-562 370 20 P.O. Box 10056 SE-181 10 Lidingö Sweden Visiting address:

Tel: +46-(0)8-562 370 00 Fax: +46-(0)8-562 370 60 P.O. Box 76 SE-340 14 Lagan Sweden Visiting address: Västergatan 4 SE-340 14 Lagan



