


MIRO TR 6.2MM SK OPTO-COUPLER MODULE


IN: 48 VDC - OUT: 48 VDC / 2 A

Transistor 2 A
48 V DC
Isolation function in output circuit
Screw terminals

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

Voltage range ON	10...48 V DC
Voltage range OFF	0...5 V DC
Control current	7 mA
LED display	LED (yellow)

General data

Housing	Black plastic, flame retardant
Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	-20...+60 °C
Dimensions H × W × D	78×6.2×65 mm

Output

Switching time ON/OFF	1/5 ms
Switching current per output	1 mA...2 A
Switching voltage	5...48 V DC
Saturation voltage (across output)	max. 0.3 V DC
Leakage current (output is open)	max. 0.3 mA
Switching frequency	max. 10/1 Hz (resist./ind.)

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1