

## Product information

# 37 43 125

### Flat Nose Pliers

For precision mechanics

DIN ISO 9655

- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding, bending and adjusting
- Tips precision-ground
- Smooth gripping surfaces
- Edges carefully deburred
- Lap joint
- Round, pointed jaws to bend wire loops
- High-grade special tool steel, forged, oil-hardened




#### General

|                 |                       |
|-----------------|-----------------------|
| Article No.     | 37 43 125             |
| EAN             | 4003773043652         |
| Pliers          | chrome-plated         |
| Head            | chrome-plated         |
| Handles         | plastic coated        |
| Weight          | 76 g                  |
| Dimensions      | 125 x 50 x 12 mm      |
| Standard        | DIN ISO 9655          |
| REACH compliant | does not contain SVHC |
| RoHS compliant  | not applicable        |

#### Technical details

|                           |         |
|---------------------------|---------|
| Jaw thickness (joint) (D) | 8.0 mm  |
| Tips width (E)            | 2.0 mm  |
| Tips thickness (F)        | 1.0 mm  |
| Jaw length (B)            | 27.0 mm |
| Head width (A)            | 14.5 mm |



technical change and errors excepted