



PRODUCT-DETAILS

## HKF-11

# HKF-11 Auxiliary Contact

---

### General Information

Extended Product Type	HKF-11
Product ID	1SAM101928R0001
EAN	4013614302237
Catalog Description	HKF-11 Auxiliary Contact
Long Description	HKF-11 Aux.-contact for front mounting

---

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85369095

---

### Popular Downloads

Data Sheet, Technical Information	1SBC100173C0201
Instructions and Manuals	2CDC131089M6801

---

### Dimensions

Product Net Width	54 mm
Product Net Height	10.5 mm
Product Net Depth /	16 mm

Length	
Product Net Weight	0.02 kg

## Technical

Terminal Type	Screw Terminals
Rated Operational Voltage	400 V AC 250 V DC Main Circuit 400 V AC
Rated Operational Current AC-15 (I <sub>e</sub> )	(120 V) 3 A (240 V) 2 A (24 V) 4 A (380 / 400 V) 1 A (500 V) 1 A
Rated Operational Current DC-13 (I <sub>e</sub> )	(125 V) 0.55 A (24 V) 2 A (250 V) 0.27 A
Rated Frequency (f)	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 1.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1/2x 0.75 ... 2.5 mm <sup>2</sup> Flexible 1/2x 0.75 ... 1 mm <sup>2</sup> Rigid 1/2x 1.0 ... 2.5 mm <sup>2</sup>
Tightening Torque	Auxiliary Circuit 0.8 ... 1.0 N·m
Wire Stripping Length	Auxiliary Circuit 8 mm
Recommended Screw Driver	Pozidriv 2
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1
Product Name	Auxiliary Contact
Suitable For	MS325 MO325
Suitable for Product Class	Manual Motor Starter
Accessory Group	Electrical
Accessory Type	Auxiliary Contact

## Technical UL/CSA

Connecting Capacity Auxiliary Circuit UL/CSA	Flexible 1/2x 14-8 AWG Stranded 1/2x 14-18 AWG
Tightening Torque UL/CSA	Auxiliary Circuit 7 in·lb
Contact Rating UL/CSA	B300 Q300

## Environmental

Ambient Air Temperature	Operation -25 ... +50 °C Storage -50 ... +80 °C
RoHS Status	Following EU Directive 2011/65/EU

## Certificates and Declarations (Document Number)

CCC Certificate	1SAA918003-3801
cUL Certificate	1SAA918002-1701
Declaration of Conformity - CE	1SAD938517-0003 1SAD938510-0037 1SAD938513-0003
GOST Certificate	1SAA918000-2703
Instructions and Manuals	2CDC131089M6801
RoHS Information	1SAD938507-0037 1SAD938514-0003
UL Certificate	1SAA918002-1601

## Container Information

Package Level 1 Width	220 mm
Package Level 1 Depth / Length	110 mm
Package Level 1 Height	195 mm
Package Level 1 Gross Weight	1.375 kg
Package Level 1 EAN	4013614441714
Package Level 1 Units	10 piece

## Classifications

Object Classification Code	Q
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC000041 - Auxiliary contact block
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
eClass	7.0 27371302
UNSPSC	39121522
IDEA Granular Category Code (IGCC)	4742 >> Electrical contacts

## Categories

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters Accessories