

PC 162515



Sample image

Order symbol: PC 162515

Product nbr: 7032740

UL Code: 7042740

UL Name: UL PC 162515

Description: Enclosure. PC


Remarks: Opaque cover

EAN: 6418074058485

El. number:

- Finland: 3435376
- Denmark: 8212002982
- Sweden: 2536132

Including: Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.



Dimensions:	Height	Width	Depth
mm:	160	250	150
inch:	6.3	9.84	5.91

Materials:

Accessories:

- TM 1625 Back Panel. for enclosures: (151 x 214 x 1)
- TRH 24 DIN-15 Mounting rail. for enclosures: (226 x 35 x 1)
- TF 28037 Mounting foot kit (4 pcs). for enclosures:
- TRH 1216 DIN-15 Mounting rail. for enclosures:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover colour: RAL 7035 -light grey
Gasket material: Polyurethane

(146 x 35 x 1)
TRM 0816 DIN-15 Mounting rail. for enclosures:
(146 x 15 x 1)
TH A Gray plastic hinges (2 pcs)

Temperatures:

Temperature °C (short term):: -40 ... 120
Temperature °C (continuous): -40 ... 80
Temperature °F (short term): -40 ... 250
Temperature °F (continuous): -40 ... 175

Rating:

Ingress protection (EN 60529): IP66; IP67;
Impact Resistance (EN 62262): IK07; IK08;
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960 °C
NEMA Class

Certificates:

SGSFimko_EURONORD