

SylSafe Spot

SylSafe Spot HR R EM3 NM MS
0041726



Product features

- SylSafe Spot HR R EM3 NM MS is a miniature emergency recessed downlight with high lumen output for high risk area illumination. Non-maintained 3 hr emergency duration with NiMH rechargeable battery. Recharge period 24 hours. Quick and easy installation with driver module and battery pack contained in articulated case that can pass through 40mm cutout. 300lm, 4W, IK03, IP30. Power Factor 0.66. Class II electrical construction.



PRODUCT OVERVIEW

Product name	SylSafe Spot HR R EM3 NM MS
Technology	LED
Type	LED
Mount	Ceiling recessed mounting
General application	Office, Hospitality, Retail, Museums & Galleries, Education
ETIM Class	EC001957
Warranty	5 years
Fixture luminous flux (lm)	300
Luminaire efficacy (lm/W)	75
Colour temperature (K)	6300
CRI (Ra)	68
Photobiological Risk Group	RG2
Luminous flux (emergency) (lm)	300
Electrical protection	Class II
Housing colour	White
IP rating	IP30
IK rating	IK03
Product EAN number	5410288417264

DATA TABLE

General data

Product name	SylSafe Spot HR R EM3 NM MS
Technology	LED
Type	LED
Mount	Ceiling recessed mounting
General application	Office, Hospitality, Retail, Museums & Galleries, Education
ETIM Class	EC001957
Warranty	5 years

Optical data

Fixture luminous flux (lm)	300
Luminaire efficacy (lm/W)	75
Colour temperature (K)	6300
CRI (Ra)	68

SylSafe Spot

SylSafe Spot HR R EM3 NM MS
0041726

Photobiological Risk Group	RG2
Luminous flux (emergency) (lm)	300
Emergency duration (h)	3

Electrical data

Mains voltage (V)	230-240V
Lamp power factor	0.66
Electrical protection	Class II
Control gear required	Yes
Drive current (mA)	53
Nominal Frequency (Hz)	50/60Hz



Physical data

Housing colour	White
IP rating	IP30
IK rating	IK03
Nominal Product Length (mm)	50
Nominal Product Width (mm)	50
Nominal Product Height (mm)	45
Weight (kg)	0.485

Packaging

Single packaging type	Carton
Product EAN number	5410288417264
Packaging single length / height (cm)	24.1
Packaging single width (cm)	11.5
Packaging single depth (cm)	5.5
DUN14 (inner)	05410288417264
DUN14 (outer)	05410288417264
Units per outer package	17
Packaging outer length / height (cm)	42.4
Packaging outer width (cm)	29.8
Packaging outer depth (cm)	28.0

PHOTOMETRY



SylSafe Spot

SylSafe Spot HR R EM3 NM MS
0041726

TECHNICAL DRAWINGS

