



Category (ETIM):	Device mount IP 54
Type:	Device mount IP54-SDGSOB LED
Order number:	18610204100
Configuration:	Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Operating device:	Electronic driver (1 pcs.)
Mains voltage:	230V / 50Hz
System performance (W):	39
Luminaire luminous flux (lm):	6000
lm/W:	149
Ambient temperatures:	-20°C / 40°C
Certifications:	IP 54, protection class I, F, D, DIN10500/Food, Indoor, CE
Colour of the housing:	traffic white RAL 9016
Weight (net) (kg):	1.9
Dimensions LxWxH/DxH (mm):	1531 x 55 x 37
mounting method:	Mounting rail system mounting
EAN-number:	4020863325832
Commodity code:	94051098


SDGSOB LED 6000lm 840 • vw • ED • 18610204100



Lighting technology
Individual.Lens.Optic-direct wide distribution
SDGSOB LED 6000 lm 840



ηLB	100 %
lm/W	149
Φ ↓/↑	98 % / 2 %
UGR q/l	20.3 / 20.7



Quick-fit mounting system Device mount IP 54; Device mount made of galvanised, profiled sheet steel, surface coated with polyester resin enamel. Toolless fastening with two integrated pressure locks. Lighttechnical element with transparent seal, end faces made of plastic, all-round closed seal to mounting rail. Housing colour traffic white RAL 9016; Direct, open light distribution, individual. lens. optic made of polycarbonate. Heat-resistant cables including fixed 3-pole rapid installation plug connector with tool-less phase pre-selection and locating finger.

Dimensions LxWxH/DxH (mm): 1531 x 55 x 37
Configuration: Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Luminaire luminous flux (lm): 6000
lm/W: 149
Operating device: Electronic driver (1 pcs.)
System performance (W): 39
Conditions: Suitable for use in ambient temperatures of -20°C to 40°C
Certifications: IP 54, protection class I, F, D, DIN10500/Food, Indoor, CE

Regiolux GmbH
Type: SDGSOB LED 6000 840 ET vw
Article number: 18610204100
Product deep link: <http://www.regiolux.de/de/article/18610204100>
5 year guarantee after registration on website.