

Nuts

For ‚Rhombus‘ T-grooves



Application:

For inserting sliding block from above through the neck of the T-groove.

Version:

- Tempered
- The reduced contact surface in the T-groove results in a lower load capacity compared with comparable DIN 508 sizes.



Art. no.	26194 020
Nominal dimension of groove	14 mm
Slot nut width	13.7 mm
Thread dimension	M12
Height	16 mm
Slot nut height	8 mm
Length	22 mm
Property class	8

EAN-Code

4020772080266