

Vertical quick-action clamp

With open clamping arm and angular base



Application:

For quick clamping of workpieces.

Version:

- Galvanised and passivated
- Stainless steel rivet
- Ergonomic, oil-resistant handle with large hand rest and soft components.

Delivery:

With tempered and galvanised thrust bolt

Art. no.	26213 020
Size	2
Hole distance	20 mm
Bore diameter	6.1 mm
Clamping height	60 mm
Retaining force	1000 N
Max. tensile force	1200 N
Thumbscrew size	M6 x 35 mm



EAN-Code

4020772090326