

Electronic 3-point quick internal micrometer

IP67



Application:

For measuring through-bores and short centring shoulders in series.

Execution:

- Self-centring and self-aligning
- Measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Max./min. value memory
- HOLD function
- Preset function
- Tolerance function

Advantage:

- Pistol grip for quick measurements using retractable lever

Delivery:

Single device with battery (1 x 3 V lithium type CR 2032) and calibration certificate in a case



Art. no.	31919 010
Brand	SYLVAC
Manufacturer Part Number	954.6013
Min./max. length measuring range	10-12.5 mm
Measuring depth	58 mm
Data transmission type	Bluetooth/Proximity
Digit increment	0.001 mm
IP protection class	IP 67
Error limit	4 µm
Display	Digital
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
DIN	863
Gross Weight	1.600 kg
Product Group	317

EAN

7640 1257 10809