

Electronic depth caliper

Series 571 with hook IP67

Mitutoyo

Application:

For measuring e.g. Drilling depths, distances to workpieces etc.

Execution:

- ORIGIN (absolute zero)
- Digimatic data output
- IP67
- Automatic deactivation after 20 minutes of non-utilisation
- With bores in the measuring bridge for connecting interchangeable measuring bridges (separate accessories)
- Depth gauge in hook version

Advantage:

- OFFSET (pressing the Offset button compensates the width of the hook)

Delivery:

In a case, including 1x SR44 battery



Art. no.	32018 265
Brand	MITUTOYO
Manufacturer Part Number	571-311-20
Min./max. length measuring range	0-150 mm
Min./max. length measuring range in inches	0-8 in
Data transmission type	DIGIMATIC
Digit increment	0.01 mm
Error limit	0.02 mm
IP protection class	IP 67
Bridge length x bridge width	250 x 10 mm
Type of locating	With locking screw
Calibration Group	B
With automatic shut off	Yes
Number of rechargeable batteries/batteries	1 PCS
Display	Digital
Battery designation	1,5 V SR44
Bridge length	250 mm
Functions	ABS function, Absolute function, Automatic switch-off, Origin (Dimension preset)
With drive wheel	No
With ABS function	Yes
With mm / inch switching	Yes
Gross Weight	0.569 kg
Product Group	3MA

EAN

4946368727240