



TUV T5

TUV 36T5 HE G5 UNP 40

TUV T5 lamps are single- or double-ended UV-C 253.7 nm emitting lamps. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

Product data

General Information	
Cap-Base	G5
Useful Life (Nom)	9,000 hour(s)
Light Technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	20 %
Operating and Electrical	
Power Consumption	40 W
Lamp Current (Nom)	0.425 A
Voltage (Nom)	97 V
Voltage (Nom)	97 V


Mechanical and Housing	
Bulb Shape	T16 [T 16mm]
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
UV	
UV-C Radiation at 100 hr	14.8 W
Product Data	
Order product name	TUV 36T5 HE G5 UNP 40
Full product name	TUV 36T5 HE G5 UNP 40
Full product code	871951429912200
Order code	928000204024
Material Nr. (12NC)	928000204024

TUV T5

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514299122
Numerator - Packs per outer box	40

EAN/UPC - Case	8719514299122
----------------	---------------

Dimensional drawing



Product	D	C
TUV 36T5 HE G5 UNP 40	16 mm	827.6 mm

