

## Cable-Eater bunched cable conduit

Cable-Eater is a cable conduit for bundling cables and conductors. Main application is the bundling and protection of cables in cable pre-assembly, electrical industry and switch cabinets.

### Info

Now also available as small PUs (2m)



Halogen-free



Assembly time

### Benefits

Reusable

Very flexible without material fatigue

Fast and easy assembly through using the cable insertion tools

### Application range

Bundling and protection for fixed and mobile electrical installations

Machines

Robot-building

Control cabinets

Office machines and systems for data processing

### Product features

Good UV-resistance

Good resistance to: alcohols, fats, mineral oils, heating oil and petrol

### Included

Suitable insertion tool

Bunches cable conduit large PUs on a roll, small PUs in bags with Euro-standard holes

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002604

ETIM 5.0 Class-Description: Cable bundle hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002604

Last Update (14.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## Cable-Eater bunched cable conduit

Note:	ETIM 6.0 Class-Description: Cable bundle hose Halogen-free Flame-retardant according to UL 94 HB
Colour delivered:	White, black, light grey
Material:	Polypropylene (PP)
Temperature range:	-30°C to +85°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**Cable-Eater bunched cable conduit**

Article number	Article description	Colour	Bundling area (mm)	Inner Ø (mm)	Panel thickness (mm)	Tool	PU (m)
61830302	SHR-08-PPW	white	6.0 - 9.0	8	0.8	STKP 8	100
61830312	SHR-15-PPW	white	10.0 - 16.0	15	0.8	STKP 15	50
61830322	SHR-20-PPW	white	17.0 - 23.0	20	0.9	STKP 20/25	30
61830332	SHR-25-PPW	white	21.0 - 25.0	25	1	STKP 20/25	20
61830333	SHR-32-PPW	white	29.0 - 32.0	32	1.3	STKP 32	15
61830300	SHR-08-PPB	black	6.0 - 9.0	8	0.8	STKP 8	100
61830310	SHR-15-PPB	black	10.0 - 16.0	15	0.8	STKP 15	50
61830320	SHR-20-PPB	black	17.0 - 23.0	20	0.9	STKP 20/25	30
61830330	SHR-25-PPB	black	21.0 - 25.0	25	1	STKP 20/25	20
61830335	SHR-32-PPB	black	29.0 - 32.0	32	1.3	STKP 32	15
61830390	SHR-08-PPG	light grey	6.0 - 9.0	8	0.8	STKP 8	100
61830391	SHR-15-PPG	light grey	10.0 - 16.0	15	0.8	STKP 15	50
61830392	SHR-20-PPG	light grey	17.0 - 23.0	20	0.9	STKP 20/25	30
61830393	SHR-25-PPG	light grey	21.0 - 25.0	25	1	STKP 20/25	20
61830394	SHR-32-PPG	light grey	29.0 - 32.0	32	1.3	STKP 32	15
Small PU							
61830401	SHR-15-PPW 2m	white	10.0 - 16.0	15	0.8	STKP 15	2
61830402	SHR-20-PPW 2m	white	17.0 - 23.0	20	0.9	STKP 20/25	2
61830403	SHR-25-PPW 2m	white	21.0 - 25.0	25	1	STKP 20/25	2
61830396	SHR-15-PPB 2m	black	10.0 - 16.0	15	0.8	STKP 15	2
61830397	SHR-20-PPB 2m	black	17.0 - 23.0	20	0.9	STKP 20/25	2
61830398	SHR-25-PPB 2m	black	21.0 - 25.0	25	1	STKP 20/25	2
61830406	SHR-15-PPG 2m	light grey	10.0 - 16.0	15	0.8	STKP 15	2
61830407	SHR-20-PPG 2m	light grey	17.0 - 23.0	20	0.9	STKP 20/25	2
61830408	SHR-25-PPG 2m	light grey	21.0 - 25.0	25	1	STKP 20/25	2

Last Update (14.12.2022)

©2022 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16