

Bench scale KERN FCB



Bench scale with second display on the backside of the scale

Features

- **Second display** on the rear of the balance
- **PRE-TARE function** for manual subtraction of a known container weight, useful for checking fill-levels
- **High mobility:** thanks to battery operation/rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations (production, warehouse, dispatch department etc.)
- **Data interface RS-232** standard
- **Protective working cover** included with delivery

Technical data

- Backlit LCD display, digit height 25 mm
- Dimensions weighing surface, stainless steel, W×D 253×227 mm
- Overall dimensions W×D×H 270×323×110 mm
- Optional battery operation, 9 V-Block not included in scope of delivery, operating time up to 12 h
- Net weight approx. 2,6 kg
- Permissible ambient temperature 5 °C/35 °C


Accessories

- **Protective working cover**, scope of delivery: 5 items, KERN FCB-A02S05
- **Rechargeable battery pack internal**, operating time up to 12 h without backlight, charging time approx. 10 h, KERN FCB-A01
- Further details, plenty of further accessories and suitable printers see *Accessories*

STANDARD



OPTION



| Model | Weighing capacity [Max] kg | Readability [d] g | Reproducibility g | Linearity g | Smallest part weight [Normal] g/piece | Option | |
|-----------|----------------------------------|-------------------------|----------------------|----------------|---|---------------|---------------------------|
| | | | | | | DAkkS KERN | DAkkS Calibr. Certificate |
| FCB 3K0.1 | 3 | 0,1 | 0,1 | ± 0,3 | 2 | 963-127 | |
| FCB 8K0.1 | 8 | 0,1 | 0,1 | ± 0,3 | 2 | 963-128 | |
| FCB 6K0.5 | 6 | 0,5 | 0,5 | ± 1,5 | 10 | 963-128 | |
| FCB 12K1 | 12 | 1 | 1 | ± 3 | 20 | 963-128 | |
| FCB 30K1 | 30 | 1 | 1 | ± 3 | 20 | 963-128 | |
| FCB 24K2 | 24 | 2 | 2 | ± 6 | 40 | 963-128 | |