



A RIPLEY® BRAND

NEW

# MC02

## 25mm Fiber Duct Cutter & Scorer

The Miller® MC02 Duct Cutter is designed to make clean, square, and burr-free ring cuts in plastic fiber ducts up to 25mm diameter. This duct cutter is ideal for cutting or scoring PVC, CPVC, HDPE, and other plastic tubing while protecting the inside fibers.

### Features

- Safe, compact & ergonomic design fits comfortably in hand for easy operation without risk of injury.
- Provides precise, burr-free cuts in plastic fiber ducts, PVC, CPVC, HDPE & other plastic tubing with diameters up to 25mm.
- Adjustable channel features three range settings: small (0-8mm), medium (9-18mm) & large (19-25mm).
- Rugged ABS construction is lightweight & durable.



### Additional Information

MODEL	PART #	ITEM DESCRIPTION	DIAMETER RANGE	COMPATIBLE MATERIALS
MC02	MC02-7000	Fiber Duct Cutter	0 - 25 mm	Plastic Fiber Ducts PVC Tubing CPVC Tubing HDPE Tubing
	MC02-7500	Replacement Blade		



Adjustable size index secures the tubing in place for precision cutting.



Recessed blade design & tool lock provides safety & protects the blade while closed.



Unique heat-treated steel blade provides square, burr-free edges during cutting operations.



Fixed stainless steel blade requires no adjustments and replace easily.

For more information or to locate the nearest authorized Ripley® distributor, please visit [www.ripley-tools.com](http://www.ripley-tools.com) or call 1 (800) 528-8665 to speak to a customer service representative.





A RIPLEY® BRAND

# Make Cable Preparation Easier

## With Additional Ripley® Products



MB03-7006



MB03-7007

### Advanced Fiber Optic Prep Kit

Complete Fiber Access Kit

Complete Kit Includes:

- Hard Plastic Case with Foam Lining **or** Zippered Nylon Tool Bag with Multiple Pouches & Belt Clip
- FO-103S Fiber Optic Stripper **or** CFS-3 Fiber Optic Stripper
- ACS+ Series Slitter for Armored & Heavy-Duty Cables
- MB04 “Twister” FTTX Drop Cable Slitter
- MSAT® 16 Series Mid-Span Fiber Access Tool
- FTS Series Buffer Tube Scorer
- KS-1 Series Fiber Optic Kevlar® Shears

PART #	MODEL	CASE TYPE
MA03-7005	Kit w/ FO-103S Fiber Optic Stripper	Hard Case with Foam Insert
MA03-7006	Kit w/ FO-103S Fiber Optic Stripper	Nylon Tool Bag with Zipper and Pockets
MA03-7007	Kit w/ CFS-3 Fiber Optic Stripper	Hard Case with Foam Insert
MA03-7008	Kit w/ CFS-3 Fiber Optic Stripper	Nylon Tool Bag with Zipper and Pockets



### CFS-3

3-Hole Fiber Optic Wire Stripper

- Three hole design efficiently removes 1.6 to 3 mm fiber jackets & buffers down to the 125 micron bare fiber
- Manufactured to precise tolerances to ensure clean, smooth strips every time
- Compliant & comfortable thermoplastic elastomer handle grips

MODEL	PART #	WIRE SIZE Ø	LENGTH
CFS-3	81300	0.063" to 0.118" (1.6 to 3 mm)	6.5" (165 mm)



### KS-1

Fiber Optic Kevlar® Shears

- Ideal for cutting Kevlar® strength fibers in fiber optic cable
- Lightweight & ergonomic design
- Micro-serrated blade reduces slippage for precise cuts

MODEL	PART #	ITEM DESCRIPTION	LENGTH
KS-1	80671	Fiber Optic Kevlar® Shears	5.5" (140 mm)
	80665	Fiber Optic Kevlar® Shears & Nylon Carrying Pouch	5.5" (140 mm)



### RCS-114 & RCS-158

Round Cable Strippers

- Designed for fast, safe & precise removal of PE, PVC, rubber & other jacket materials
- Spring-loaded cable brace firmly secures cable against the blade for controlled cutting action
- Durable blade performs rotary & spiral type cuts

MODEL	PART #	CABLE SIZE Ø	REPLACEMENT BLADE	
RCS-114	37140	0.178" to 1.14" (4.5 to 29.0 mm)	CB231	37150
RCS-158	37145	0.75" to 1.58" (19.0 to 40.0 mm)		

LIT-ML-0009 REV. 00



RIPLEY TOOLS, LLC. • 46 NOOKS HILL ROAD • CROMWELL, CT 06416 USA

P: +1 (800) 528-8665 F: (860) 635-3631 W: WWW.RIPLEY-TOOLS.COM