


Datasheet

V1_09072017_01_en

Item no. 1523972 (Yellow), 1523973 (Green): 2.5mm(W) X 100mm(L)
 1523974 (Yellow), 1523975 (Green): 2.5mm(W) X 150mm(L)
 1523976 (Yellow), 1523977 (Green): 2.5mm(W) X 200mm(L)
 1523978 (Yellow), 1523979 (Green): 2.8mm(W) X 250mm(L)
 1524006 (Yellow), 1523980 (Green): 2.8mm(W) X 300mm(L)



Model	Description		Color	Material	E: Bundle Diameter(mm)	Tensile Strength	
	L(mm)	W(mm)				LBS	KGS
2.5*100	100 ± 3	2.5	yellow/green	UL approved nylon 66, fireproof grade 94V-2, acid- resisting, anti-corrosion, good insulation, not easy aging, strong bearing capacity.	2-22	18	8
2.5*150	150 ± 4.5	2.5			2-35		
2.5*200	200 ± 6	2.5			2-50		
2.8*250	250 ± 7.5	2.8			3-65	26	12
2.8*300	300 ± 9	2.8			3-80		

Fluorescent Cable Tie

Operating Temperature & Humidity: 5°C to 75°C 10 – 90%

Storage Temperature & Humidity: 5°C to 75°C 10 – 90%

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.