

## Han-Eco Cable gland M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 5111
Specification	Han-Eco Cable gland M20
HARTING eCatalogue	<a href="https://b2b.harting.com/19410005111">https://b2b.harting.com/19410005111</a>

### Identification

Category	Accessories
Series of hoods/housings	Han-Eco®
Type of accessory	Cable gland

### Technical characteristics

Tightening torque	4 Nm Fitting 3 Nm Cap nut
Wrench size	24
Limiting temperature	-40 ... +125 °C
Size	M20
Clamping range	6 ... 13 mm

### Material properties

Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel



**Pushing Performance**  
Since 1945

## Material properties

Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Commercial data

Packaging size	2
Net weight	1 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140192997
eCl@ss	27140801 Screwed cable gland (electrical)