


MPR67+ REPEATER PROFIBUS DP 3 SEGMENTS

Repeater PROFIBUS DP + PROFIsafe
3 segments
Protection IP67

Housing fully potted. For connection cables please see chapter "Connection Technology"

[Link to Product](#)

Illustration



Product may differ from Image

Technical Data

Operating voltage	24 V DC (EN 61131-2)
Module Supply	via PIN 4 sensor supply (7/8" power)
Current consumption	approx. 80 mA
Transfer rate	to 12 Mbit/s

General data

Protection	IP67
Mounting method	2-hole screw mounting
Temperature range	0...+55 °C (storage temperature -20...+75 °C)
Dimensions H × W × D	151×30×34.5 mm

Diagnostic

Communication status	per LED and BUS
----------------------	-----------------

Commercial data

country of origin	DE
customs tariff number	85176200
minimum order quantity	1