


ADAPTOR M12 MALE 5 POLE/ M12 FEMALE 3 POLE SHIELDED

For analog sensors

Adapter
M12 - M12
Male straight to female straight
5-pole, shielded

[Link to Product](#)

Illustration



Product may differ from Image

Form

42271

Technical Data

Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Compression gland	Zinc die casting, matte nickel plated
Protection	IP67 inserted and tightened (EN 60529)
Material	PUR

General data

Temperature range	-25...+85 °C
-------------------	--------------

Test isolation voltage	0.8 kVrms
------------------------	-----------

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1