

16927102. - verso maintenance trolley


Short Description

verso maintenance trolley with 10 drawers and top tray

WxDxH: 1050x550x965mm

Product Images





Description	verso maintenance trolley with 10 drawers & top tray with mat. Featuring a robust, fully welded steel housing with double, independent, storage sections, push - pull handles, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 4x 100mm, 6x 175mm (50kg U.D.L.). Finished in durable powder coat paint. WxDxH: 1050x550x965mm
Width	1050
Depth	550
Height	965
Customs tariff number	94032080
Product material	Sheet steel
Product surface	Powder coated
Drawer Load Capacity	50 kg
Drawer height 1	100mm
Drawer 1 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 2	100mm
Drawer 2 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 3	175mm
Drawer 3 Internal Dimensions	930mm x 430mm x 150mm
Drawer height 4	175mm
Drawer 4 Internal Dimensions	930mm x 430mm x 150mm
Drawer height 5	175mm
Drawer 5 Internal Dimensions	930mm x 430mm x 150mm
Drawer height 6	100mm
Drawer 6 Internal Dimensions	930mm x 430mm x 75mm
Drawer height 7	100mm
Drawer 7 Internal Dimensions	930mm x 430mm x 75mm
Additional Information Drawer height 8	175mm
Drawer 8 Internal Dimensions	930mm x 430mm x 150mm

Drawer height 9	175mm
Drawer 9 Internal Dimensions	930mm x 430mm x 150mm
Drawer height 10	175mm
Drawer 10 Internal Dimensions	930mm x 430mm x 150mm
Door type	Plain

Product Options

Colour:	Anthracite grey
	Crimson red
	Gentian blue
	Light grey