



AOH(X) & AOH(X) .. G

Generic code	Rubix engineering code	d1	d2	l	a	G	b	g	e	t	Weight (kg)	Dismounting nut	Locknut	Locking device
AH2356-AKN	891174	260	280	212	8	Tr 310x5	30	-	-	-	21.60	HM62T-AKN	HM52T-AKN	MB52-AKN
AOH2356-AKN	891251	260	280	212	8	Tr 310x5	30	G1/4	11	15	21.60	HM62T-AKN	HM52T-AKN	MB52-AKN
AOH2356G-AKN	890590	260	280	212	8	Tr 300x5	30	G1/4	9	15	20.00	HM3160-AKN	HM52T-AKN	MB52-AKN
AH3060-AKN	890518	280	300	145	8	Tr 320x5	26	-	-	-	14.40	HM3064-AKN	HM56T-AKN	MB56-AKN
AOH3060-AKN	891269	280	300	145	8	Tr 320x5	26	G1/4	9	15	14.40	HM3064-AKN	HM56T-AKN	MB56-AKN
AOH24060-AKN	891256	280	300	184	18	Tr 310x5	24	G1/8	7	12	15.50	HM62T-AKN	HM56T-AKN	MB56-AKN
AOH24060G-AKN	890593	280	300	184	18	Tr 320x5	24	G1/8	7	12	16.40	HM3164-AKN	HM56T-AKN	MB56-AKN
AH3160-AKN	891227	280	300	192	8	Tr 330x5	30	-	-	-	20.80	HM66T-AKN	HM56T-AKN	MB56-AKN
AOH3160-AKN	891280	280	300	192	8	Tr 330x5	30	G1/4	11	15	20.80	HM66T-AKN	HM56T-AKN	MB56-AKN
AOH3160G-AKN	891281	280	300	192	8	Tr 320x5	30	G1/4	9	15	20.80	HM3164-AKN	HM56T-AKN	MB56-AKN
AOH24160-AKN	891262	280	300	224	18	Tr 320x5	24	G1/4	9	15	20.80	HM3164-AKN	HM56T-AKN	MB56-AKN
AOH3260-AKN	891282	280	300	228	8	Tr 330x5	34	G1/4	12	15	26.00	HM66T-AKN	HM56T-AKN	MB56-AKN
AH3064-AKN	891201	300	320	149	8	Tr 345x5	27	-	-	-	16.00	HML69T-AKN	HM3060-AKN	MS3060-AKN
AOH3064-AKN	891270	300	320	149	8	Tr 345x5	27	G1/4	10	15	16.00	HML69T-AKN	HM3060-AKN	MS3060-AKN
AOH3064G-AKN	890599	300	320	149	8	Tr 340x5	27	G1/4	9	15	15.60	HM3068-AKN	HM3060-AKN	MS3060-AKN
AH3264-AKN	891235	300	320	246	8	Tr 350x5	36	-	-	-	30.60	HM70T-AKN	HM3060-AKN	MS3060-AKN
AOH3264-AKN	891283	300	320	246	8	Tr 350x5	36	G1/4	12	15	30.60	HM70T-AKN	HM3060-AKN	MS3060-AKN
AH3068-AKN	891202	320	340	162	9	Tr 365x5	28	-	-	-	19.50	HML73T-AKN	HM3064-AKN	MS3064-AKN
AOH3068-AKN	890600	320	340	162	9	Tr 365x5	28	G1/4	10	15	19.50	HML73T-AKN	HM3064-AKN	MS3064-AKN
AOH3068G-AKN	891273	320	340	162	9	Tr 360x5	28	G1/4	9	15	19.00	HM3072-AKN	HM3064-AKN	MS3064-AKN
AH3268-AKN	891236	320	340	264	9	Tr 370x5	38	-	-	-	35.40	HM74T-AKN	HM3064-AKN	MS3064-AKN
AOH3268-AKN	891284	320	340	264	9	Tr 370x5	38	G1/4	13	15	35.40	HM74T-AKN	HM3064-AKN	MS3064-AKN
AH3272-AKN	891237	340	360	274	9	Tr 400x5	40	-	-	-	41.50	HM3180-AKN	HM3068-AKN	MS3064-AKN