


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/3/13	D.GRIFFIN



"P1"
MALE 9-PIN
D-SUB CONNECTOR

"J1"
FEMALE 9-PIN
D-SUB CONNECTOR

"P1"	WIRE COLOR	"J1"
1	BLACK	1
2	RED	2
3	ORANGE	3
4	YELLOW	4
5	GREEN	5
6	BLUE	6
7	VIOLET	7
8	GRAY	8
9	BROWN	9
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FT	METERS
CSPL9MF-2.5	2.5	0.76
CSPL9MF-5	5.0	1.52
CSPL9MF-10	10.0	3.05
CSPL9MF-15	15.0	4.57
CSPL9MF-25	25.0	7.62
CSPL9MF-50	50.0	15.24

NOTES:

- CABLE : UL STYLE 2919, 9 CONDUCTOR (26AWG) (DOUBLE SHIELDED, BRAID & FOIL) JACKET: PVC, COLOR: LIGHT GRAY (PANTONE 400C)
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D.PARHAM CHECKED BY D.DESJARDIN APPROVED BY S.SMITH	DATE 05/05/2011 01/04/2013 01/04/2013	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY D-SUBMINIATURE
	PROJECTION 			PRODUCT DESCRIPTION CA DB9M/F PLAS ARMOR
	COLOR VARIATIONS MAY OCCUR			SIZE A
CS2N-FS01		FSCM NO. 43321	DWG. NO. CSPL9MF	
SCALE: NONE		CAD FILE: CSPL9MF.SLDDRW		
SHEET 1 OF 1		REV. A		