

HAN CGM-P F+B M25X1,5 D. 13-16 nature



Image is for illustration purposes only. Please refer to product description.

Part number	19 15 523 5197
Specification	HAN CGM-P F+B M25X1,5 D. 13-16 nature
HARTING eCatalogue	https://b2b.harting.com/19155235197

Identification

Category	Accessories
Series of hoods/housings	Han [®] F+B
Type of accessory	Cable gland

Version

Pack contents	With spacing washer
---------------	---------------------

Technical characteristics

Limiting temperature	-40 ... +100 °C
Wrench size	32
Degree of protection acc. to IEC 60529	IP67 / IP69
Size	M25
Clamping range	13 ... 16 mm

Material properties

Roughness of the surface	≤0.8 µm
Colour (seal)	Blue
Material (cable glands)	Polyamide (PA)
Material (accessories)	VA 1.4305
Colour (accessories)	White
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	Ecolab Topactive 200
	Ecolab Topactive 500
	Ecolab Topax 66
	Ecolab Topactive OKTO
	Ecolab Topax 990
	FDA 21 CFR 177.1500
	FDA 21 CFR 176.170 (c)
	FDA 21 CFR 177.1390
	FDA 21 CFR 177.1395
	FDA 21 CFR 177.2600

Commercial data

Packaging size	1
Net weight	0.1 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27144432 Screwed cable gland (electr.)