

Electronic micrometer

with caliper jaw

Mitutoyo

Application:

For measuring hard-to-reach places.

Execution:

- carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench, battery



Art. no.	32017 520
Brand	MITUTOYO
Manufacturer Part Number	343-250-30
Display	Digital
Min./max. length measuring range	0-25 mm
Digit increment	0.001 mm
Measuring surface diameter	6.3 mm
Measuring arrangement	Outer beaks
Material of measuring bolt	Carbide
IP protection class	IP 40
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Hold-function (AE lock), Automatic switch-off
Min./max. measurement force	1-6 N
Error limit	5 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	0.710 kg
Product Group	3MA

EAN

4946368689692