

## Workbench undercounter cabinet with 8 drawers

Height 710 mm, width 570 mm, drawers with full extension

### Application:

For the individual assembly of a workbench with workbench panel and base.

### Execution:

- Solidly welded steel sheet construction
- Drawers with high-quality Delrin rollers
- Drawers with slots all around for inserting compartment rails and dividers
- Drawers with slotted sheet steel bottom for attaching and fixing individual items
- Drawers flush with cabinet housing, no protruding grip handles
- Aluminium grip handles with paper and cellophane strips and lateral cover caps
- Central locking with rotary cylinder security lock, incl. 2 keys
- Suitable insert material for drawers, see no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010



<b>Art. no.</b>	<b>50212 417</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50212417
<b>Number of drawers</b>	8 PCS
<b>Pullout type</b>	Full extension
<b>Height</b>	710 mm
<b>Width</b>	570 mm
<b>Depth</b>	680 mm
<b>Drawer width (inner dimension)</b>	450 mm
<b>Drawer depth (inner dimension)</b>	600 mm
<b>With single pull-out safety brake</b>	Yes
<b>Load-carrying capacity per drawer</b>	70 kg
<b>Drawer surface</b>	0.27 m <sup>2</sup>
<b>With doors</b>	No
<b>Drawer with slots</b>	Yes
<b>Perforated drawer base</b>	Yes
<b>Central locking</b>	Yes
<b>Lock type</b>	DOM® locking system
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Optional
<b>Colour of front</b>	Optional
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	0.680 kg
<b>Product Group</b>	5BC

### EAN

4039247969272