

Workbench trolley with lowerable transport wheels, working height 840 mm

Drawers with option of partial of full extension

Application:

The mobile workstation with versatile options for use.

Execution:

- Welded sheet steel construction equipped with one workbench top panel made of solid beechwood, 40 mm thick
- With integrated lowering device for stationary use
- Suitable insert material for drawers, see no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

Advantage:

- The workbench can easily be lifted and lowered by simply turning the lever on the front side
- The workbench trolley is absolutely stable when lowered
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50285 241
Brand	HK
Manufacturer Part Number	50285241
Number of fixed rollers	2 PCS
Working height	882 mm
Number of steering rollers	2 PCS
Worktop width	1660 mm
Number of drawers	8 PCS
Worktop height	40 mm
Worktop depth	700 mm
Pullout type	Partial extension
On castors	Yes
Moving device, can be lowered	Yes
Colour of front	Anthracite grey RAL 7016
Cabinet colour	Light grey RAL 7035
With single pull-out safety brake	Yes
Surface	Powder-coated
With wheel lock	Yes
Load-carrying capacity	720 kg
Dynamic load-carrying capacity	540 kg
Wheel diameter	160 mm
Type	mobile/retractable
Lock type	DOM® locking system
Material of worktop	Solid beech
Drawer front height	2 x 60 mm, 2 x 90 mm, 2 x 150 mm, 2 x 180 mm
Material	Sheet steel
Drawer width (inner dimension)	450 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	450 x 600 mm
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	100 kg
Material of wheel	Solid rubber
Central locking	Yes
Gross Weight	100.000 kg
Product Group	501

EAN

4053625403349