

## Ring bolt incl. Key

Screwable sling point, 360° rotation

CARTEC

### Application:

For the safe attachment of loads.

### Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

### Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing
- Tool-free assembly

### Delivery:

Includes Key



|  |                  |
|--|------------------|
| <b>Art. no.</b>  | <b>77232 236</b> |
| <b>Brand</b>   | CARTEC           |
| <b>Manufacturer Part Number</b>                                    | C807XCHT36       |
| <b>Design</b>  | With key         |
| <b>Thread dimension</b>  | M36              |
| <b>Load-carrying capacity</b>                                      | 7 t              |
| <b>Distance between lower edge of retainer holder and retainer</b> | 105 mm           |
| <b>Bracket width</b>   | 30 mm            |
| <b>Bracket height</b>  | 32 mm            |
| <b>Outer diameter</b>  | 135 mm           |
| <b>Diameter 2</b>  | 96.5 mm          |
| <b>Internal width</b>  | 74 mm            |
| <b>Width of support plate</b>                                      | 77 mm            |
| <b>Usable thread length</b>  | 55 mm            |
| <b>Width across flats</b>  | 22 mm            |
| <b>Weight</b>  | 3.4 kg           |
| <b>Gross Weight</b>  | 3.598 kg         |
| <b>Product Group</b>   | 775              |

### EAN

8013429916908