



PeakTech 6035 D
0 - 30 V DC / 0 - 2,5 A DC

1CH LED Display DC Output FIXED Output Linear Power Supply

PeakTech® 6015 A
0 - 30 V DC / 0 - 5 A DC

1CH Analog Display DC Output Linear Power Supply



Serie von linear geregelten, stabilisierten Labornetzgeräten. 3-stellige 14 mm blaue LED-Anzeigen bzw. übersichtliche Analog-Anzeigen ermöglichen eine schnelle und präzise Ablesung der eingestellten Werte. 4 mm Sicherheitsbuchsen, ein Metallgehäuse, Kurzschlussfestigkeit und Überlastschutz zeichnet diese neue Serie besonders aus.

- Ausgangsspannung und Ausgangsstrom kontinuierlich veränderbar
- Überlastschutz und kurzschlussfest
- Sicherheit: EN 61010-1
- Zubehör: Netzkabel, Bedienungsanleitung



Series of linear regulated, stabilized power supplies. 3 digit 14 mm blue LED-displays or analogue displays enable the user to read the fixed values very fast and precise. 4 mm safety jacks, short circuit and over-voltage protection as well as metal cabinet are main features of this new series. The one-channel versions are provided with fine adjuster for the output voltage.

- Output voltage and current continuously adjustable
- Short-circuit and overload protected
- Safety: EN 61010-1
- Accessories: Power cable, Manual

► SPECIFICATIONS	P 6015 A	P 6035 D
Anzeige Display	Analog / Analogue	Digital LED
Ausgangsspannung / Output voltage	0-30 V DC	0-30 V DC 5V / 0,5 A fest/fixed 12 V / 0,5A fest/fixed
Ausgangsstrom / Output current	0-5 A DC	0-2,5 A DC
Ausgangsleistung / Output power	150 W	75 W
Restwelligkeit U / Residual ripple U	< 1 mV eff/rms	< 1 mV eff/rms
Restwelligkeit I / Residual ripple I	3 mA eff/rms	3 mA eff/rms
Betriebsspannung / Operation voltage	115 V / 230 V AC; 50/60 Hz	
Abmessungen / Dimensions (BxHxT/WxHxD)	135 x 155 x 285	170 x 155 x 285
Gewicht / Weight	5,5 kg	5,3 kg