

iHF LED outdoor lights with invisible sensor

New - available January 2013

- Design sensor outdoor light with revolutionary sensor technology
- You don't see it. It sees you.
- Hidden HF-technology for outdoors
- LED sensor up-/downlights of a special kind
- LED and sensor. Maximum savings, never change bulbs again.

Technical data

Voltage:	230 – 240 V, 50 Hz
LED Output:	8/12W LED
Luminous flux:	400/600 Lumen
Light colour:	3000 Kelvin
LED lifetime:	50.000 hours
HF-technology:	5,8 GHz
Angle of detection:	180°
Reach:	2 - 5 m (radial)
Twilight setting:	2 – 2000 Lux
Time setting:	5 sec. – 15 min.
IP class:	IP 44
Material:	Aluminium/plastic

EAN-Code	Art.-No.	Bezeichnung/Description
4007841 671419	671419	L 800 iHF LED Downlight
4007841 671310	671310	L 810 iHF LED Up-/Downlight
4007841 671327	671327	L 820 iHF LED Up-/Downlight HN



L 800 iHF LED



L 810 iHF LED



L 820 iHF LED

