

Pluggable Terminal Blocks

5 mm Pitch, Reversed



Reversed (Latches are on wire entry side)

Polarised mouldings

Withstand Voltage - AC2000V/1Min

Guided pin alignment

SPECIFICATION:

| | |
|--------------------------|-------------------------------------|
| Gender of contacts | Female |
| Rated current to EN | 15 A |
| Pitch | 5 mm |
| Component type | Wire plug straight |
| Termination type | Screw Connection |
| Connection direction | vertical |
| Rated voltage to EN | 250 V |
| Combustibility class | UL 94 V-0 |
| Colour | green |
| Temperature range | -33...+120 °C |
| Cross-section max. | 3.3 mm ² |
| Cross-section min. | 0.2 mm ² |
| Connection cross-section | 0.2-3.31 mm ² (24-12AWG) |

PRODUCT RANGE:

| Art. Nr. | Poles | A | Length |
|---------------|-------|-------|--------|
| RND 205-00342 | 2 | 10 mm | 10 mm |
| RND 205-00343 | 3 | 15 mm | 15 mm |
| RND 205-00344 | 4 | 20 mm | 20 mm |
| RND 205-00345 | 5 | 25 mm | 25 mm |
| RND 205-00346 | 6 | 30 mm | 30 mm |
| RND 205-00348 | 8 | 40 mm | 40 mm |
| RND 205-00349 | 9 | 45 mm | 45 mm |