

Beacon LED XXL

BEACON XXL NB DALI 3K L3 WHT

2092995



Product features

- 2092995 BEACON XXL NB DALI 3K L3 WHT Integrated LED spotlight, white RAL 9016, compact and minimalist design, ideal for double height spaces, retail and display applications, die-cast aluminium body, passive cooling heatsink, beam angle: 21° narrow beam, optics: Fresnel lens for controlled beam, colour temperature: 3000K warm white, total system power: 48W, total fixture output: 3713lm, luminaire efficacy: 77lm/W, LOR: 100%, colour rendering: Ra 93 typical, LED Chromacity: 3 step MacAdam ellipse, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 1200mA, electronic driver, DALI dimmable, power factor: 0.95 electrical protection: CLASS I, DALI track adaptor, suitable for Concord Lytespan DALI track, ingress protection rating: IP20. IMPORTANT NOTE: This fixture can only be used on the Lytespan DALI or Lytebeam DALI tracks !



PRODUCT OVERVIEW

Product name	BEACON XXL NB DALI 3K L3 WHT
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Retail
ETIM Class	EC001744
E-number FI	4278673
E-number SE	7401085
Warranty	5 years
Fixture luminous flux (lm)	3713
Luminaire efficacy (lm/W)	77.35
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	93
Colour Consistency (SDCM)	3
Beam Angle (°)	21
Photobiological Risk Group	RG1
Total power consumption (W)	48
Product Voltage (V)	240
Electrical protection	Class I
Control gear type	Electronic ballast
Dimmable	Yes
Dimming method	DALI
Housing colour	White
IP rating	IP20
Product EAN number	5025768929955

Beacon LED XXL

BEACON XXL NB DALI 3K L3 WHT
2092995

DATA TABLE

General data

Product name	BEACON XXL NB DALI 3K L3 WHT
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number FI	4278673
E-number SE	7401085
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3713
Luminaire efficacy (lm/W)	77.35
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	93
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Beam Angle (°)	21
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	48
Mains voltage (V)	220-240V
Product Voltage (V)	240
Lamp power factor	0.95
Electrical protection	Class I
Control gear type	Electronic ballast
Transformer required	Yes
Dimmable	Yes
Dimming method	DALI
Drive current (mA)	1200
Inrush Current (A)	30
Energy Efficiency Class (A->G) of contained light source	E
Max. Luminaires per 10A B Breaker	13
Max. Luminaires per 16A B Breaker	20

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	55500

Beacon LED XXL

BEACON XXL NB DALI 3K L3 WHT
2092995


Physical data

Housing colour	White
IP rating	IP20
Diffuser finish	Diffuse
Diffuser material	PMMA Acrylic
Reflector finish	None
Nominal Product Length (mm)	85
Nominal Product Width (mm)	168
Nominal Product Height (mm)	205
Nominal Product Diameter (mm)	113
Weight (kg)	1.443

Packaging

Single packaging type	Carton
Product EAN number	5025768929955
Packaging single length / height (cm)	25.0
Packaging single width (cm)	19.5
Packaging single depth (cm)	20.0
DUN14 (outer)	05025768929955
Units per outer package	1
Packaging outer length / height (cm)	25.0
Packaging outer width (cm)	19.5
Packaging outer depth (cm)	20.0

PHOTOMETRY



Distance [m]	Cone diameter [m]	E(0°) E(C0)	E(10.3°)	Illuminance [lx]
0.5	0.18	68429	26459	
1.0	0.36	14907	7114	
1.5	0.55	6492	3152	
2.0	0.73	3692	1778	
2.5	0.91	2307	1138	
3.0	1.09	1623	790	

Distance [m] Cone diameter [m] Illuminance [lx]
C0 - C180 (Half beam angle: 20.6°)

TECHNICAL DRAWINGS

