

HSS metal circular saw blade

for universal use up to 1000 N/mm² on Eisele and Trennjäger machines

ORION[®]

Application:


for creating saw cuts on low-speed machines such as Eisele, Trennjäger and other brands.

Execution:

- precision-ground metal circular saw blade with Bw tooth type (curved tooth = alternate bevel) and C tooth type (with taper tap and third tap)

Advantage:

- innovative cutting geometry for cutting solid material with high cutting depths
- cut distribution enables high cutting performance
- steam-treated protects against metal welding



Art. no.	14015 096
Brand	ORION
Manufacturer Part Number	14015096
Tooth shape	C
Cutting material	HSS
Cutting edge diameter	250 mm
Bore diameter	32 mm
Thickness of cutting edge	2 mm
Teeth spacing	6 mm
Side holes	2/8/45, 2/9/50, 2/11/63
Number of teeth	128
Gross Weight	0.684 kg
Product Group	1QK

EAN

4053625362837