

Nuts

For ‚Rhombus‘ T-grooves



Application:

For inserting sliding block from above through the neck of the T-groove.

Version:

- Tempered
- The reduced contact surface in the T-groove results in a lower load capacity compared with comparable DIN 508 sizes.



Art. no.	26194 040
Nominal dimension of groove	18 mm
Slot nut width	17.7 mm
Thread dimension	M16
Height	20 mm
Slot nut height	10 mm
Length	28 mm
Property class	6

EAN-Code

4020772080280