

META COMPACT single-sided office boltless rack



Application:

Clearly arranged storage of binders. Ideal for archives and offices.

Execution:

- zinc-plated, with disassembled frame or coated in light grey RAL 7035, with clinched/ pre-assembled frame
- quick boltless assembly without tools
- Basic rack, can be expanded as required using an add-on rack
- Shelves complete with end stop (optional cover shelf without end stop)
- Shelves/profiles made of high-quality steel, shelves adjustable in increments of 25 mm
- with steel feet suitable for anchoring
- Shelf height is more than 5 times the shelf width!
- Basic rack planning dimensions: Nominal length + 56 mm, nominal depth + 36 mm add-on rack planning dimensions: Nominal length + 6 mm, nominal depth + 36 mm



Art. no.	50166 235
Brand	META
Manufacturer Part Number	20077634
Height	1850 mm
Length	1056 mm
Depth	336 mm
Nominal length	1000 mm
Nominal depth	300 mm
Type of shelving	Shelving unit
Design	One side
Type of assembly	To insert
Surface	Plastic-coated
ESD-capable	No
Design of the frame	Pre-assembled
Grid dimension	25 mm
Number of shelves	5 PCS
Load-carrying capacity per shelf	80 kg
Number of frame	2 PCS
Quality label	RAL-RG 614/1
Made in	Germany
Product certification	Institute for Materials Research and Testing (MPA) North Rine Westphalia (NRW) (Dortmund)
Approval mark	GS - MPA NRW
Approval mark - Product certification	GS - MPA NRW - Institute for Materials Research and Testing (MPA) North Rine Westphalia (NRW) (Dortmund)
Gross Weight	25.180 kg
Product Group	508

EAN

4026212133325